

SERIES WHU2ER METAL-CASED HEATING MANTLES FOR ROUND-BOTTOM FLASKS

$T_{max} = 450^{\circ}C$

- powder coated, robust metal housing with high chemical resistance
- hand crocheted heating unit made of glass silk

Device features

- integrated heating zone switch
 - heating zone 1 or heating zone 1+2;
- integrated power selector
 - ON and OFF function
 - infinitely variable power (0-100%)
- detachable plug-in connection (cable length 0.5 m)
- RCD safety plug (cable length 1.0 m)

Accessories ▶ Page 12

- rod clamp STK 2
 - for mounting set-ups



2 heating zones

!NEW!



| Volumen (ml) | Flask Ø (mm) | Power (W ±10%) | Heating zones | Base opening Ø × H (mm) | Artikel-Nr. 230 VAC* | Price (€) | Delivery code |
|--------------|--------------|----------------|---------------|-------------------------|----------------------------|-----------|---------------|
| 4.000 | 207 | 700 | 2 | 288 × 166 | WHU2ERXX-230XX450-004000RC | 655,00 | C |
| 5.000 | 223 | 860 | 2 | 318 × 166 | WHU2ERXX-230XX450-005000RC | 755,00 | C |
| 6.000 | 236 | 1.000 | 2 | 318 × 166 | WHU2ERXX-230XX450-006000RC | 759,00 | C |
| 10.000 | 279 | 1.400 | 2 | 368 × 194 | WHU2ERXX-230XX450-010000RC | 855,00 | C |
| 20.000 | 345 | 2.000 | 2 | 438 × 234 | WHU2ERXX-230XX450-020000RC | 1158,00 | C |

*115 V on request



Laboratory set-up option (from left to right) with PILZ® heating mantle WHU2ER 6,000 ml with rod clamp STK 2 and PILZ® heating mantle WHG2 50 ml with support ring.